

**SKU:**

**Price:** ₹37,000.00

**Stock:** instock

**Categories:** [Biology](#)



## Product Description

### SINGLE STAGE DISTILLATION



The apparatus consists of a purity quartz with built-in cleaning of deposits, a boiler with receiving coil, and a Safety Control Unit (SCU) which has safety parts in case of water leak. It can withstand thermal shock proof.



# AGN ENTERPRISES

MANUFACTURER & SUPPLIER  
ALL KINDS OF LABORATORY EQUIPMENTS



"AU the parameters are under Standard Test Conditions' Advantages

- Rust proof powder coated sturdy stand as
- Replaceable clamps are provided for

alignment of the boiler and condenser. Advanced Feattres

- Distillate is pyrogen free; also it is free of heavy metals.
- Switch on time is less than minute providing distilled water instantly.
- Low maintenance is



# AGN ENTERPRISES

MANUFACTURER & SUPPLIER  
ALL KINDS OF LABORATORY EQUIPMENTS



## Quartz Condenser

	Output Capacity (Approx.)	Power Rating (Total)	Cooling Water
SD-25Q	2.5Ltr/Hr	2 KW	40 Ltr/Hr
SD-50Q	5 Ltr/Hr	4.4 KW	65 Ltr/Hr
SD-80Q	8 Ltr/Hr	6 KW	90 Ltr/Hr
SD-100Q	10 Ltr/Hr	9 KW	120 Ltr/Hr

■ Indicates 3 Phase

## Safety Cut Off Device (Digital Safety Control Unit with Alarm)

SCU-1	2 Ltr/Hr
SCU-2	5,8 & 10 Ltr/Hr

\*\* It is recommended to use Water Softener Unit with All types of water distillations for desired output, good quality distillate & long life.

[Read More](#)

**SKU:**

**Price:** ₹36,000.00

**Stock:** instock

**Categories:** [Water Still/Distillation Unit](#)

## Product Description

The apparatus consists of a boiler made from high purity quartz with built in discharge joint for easy cleaning of deposits. A spiral condenser is fitted on the boiler with receiving adapter. The unit comes with Safety Control Unit (Optional) to protect the Glass parts in case of water failure or overheating. Quartz can withstand high temperature and is thus thermal shock proof.

"AU the parameters are under Standard Test Conditions' Advantages

- Rust proof powder coated sturdy stand as
- Replaceable clamps are provided for

alignment of the boiler and condenser. Advanced Feattres

- Distillate is pyrogen free; also it is free of heavy metals.
- Switch on time is less than minute providing distilled water instantly.
- Low maintenance is

## Borosilicate Condenser

	Output Capacity (Approx.)	Power Rating (Total)	Cooling Water Consumption (App.)	
SD-25B	2.5Ltr/Hr	2 KW	40 Ltr/Hr	36000.00
SD-50B	5 Ltr/Hr	4.4 KW	65 Ltr/Hr.	60000.00
SD-80B	8 Ltr/Hr	6 KW	90 Ltr/Hr	86000.00
SD-100B	10 Ltr/Hr	9 KW	120 Ltr/Hr	100000.00

## Quartz Condenser

	Output Capacity (Approx.)	Power Rating (Total)	Cooling Water Consumption (App.)	
SD-25Q	2.5Ltr/Hr	2 KW	40 Ltr/Hr	55000.00
SD-50Q	5 Ltr/Hr	4.4 KW	65 Ltr/Hr.	100000.00
SD-80Q	8 Ltr/Hr	6 KW	90 Ltr/Hr	130000.00
SD-100Q	10 Ltr/Hr	9 KW	120 Ltr/Hr	180000.00

■ Indicates 3 Phase

## Safety Cut Off Device (Digital Safety Control Unit with Alarm)

SCU-1	2 Ltr/Hr	20000.00
SCU-2	5,8 &10 Ltr/Hr	22000.00

\*\* It is recommended to use Water Softener Unit with All types of water distillations fo  
desired output, good quality distillate & long life.

[Read More](#)

**SKU:**

**Price:** ₹36,000.00

**Stock:** instock

**Categories:** [Biotechnology](#)



## Product Description

### POLISHING Metallurgical Disc (Variab

Used for Rough & F  
Specimen is held ag  
a polishing cloth im  
media such as silico  
polishing gives the  
finish. The disc con  
on steel spindle.The  
ball bearing. The di  
changing of polishin  
on the disk by mean  
the rim of disc. Aro  
fitted with drain tub  
to 1500 RPM. Work



**Categories:** [Metallurgy](#)

## Product Description

Used for Rough & Fine Polishing of Specimens. The Specimen is held against a rotating flat disk, on which a polishing cloth impregnated with suitable polishing media such as silicon carbide powder is stretched. Disc polishing gives the specimen scratch free mirror like finish. The disc consists of 20cm balance disc mounted on steel spindle. The spindle is located on heavy duty ball bearing. The disc is easily removable for quick changing of polishing cloth or paper, which is fastened on the disk by means of a spring or rubber gridle on the rim of disc. Around the disc is a S.S drain jacket fitted with drain tube. Continuously variable Speed 300 to 1500 RPM. Works on 220V Single Phase AC Supply.

## TABLET MAKING MACHINE (Punching Machine) Hand Operated



SINGLE PUNCH for making Tablets up to 1000 mg as per size of die & punch 6, 9 & 12 mm (Any one). Automatic compression & ejection device with each revolution of the wheel drive. Built on heavy cast iron body with eccentric pressure system. Stainless steel hopper provided & connected by a Rubber tube. Easy setting for thickness & hardness of tablets with lock nuts. Die & set of punches are chromium steel.

[Read More](#)

**SKU:**

**Price:** ₹36,000.00

**Stock:** instock

**Categories:** [Pharmacy](#)

## Product Description

## DISTILLATION APPARATUS (ALL GLASS) Triple Stage having flask of cap. 3 Litre



Automatic Electrically Heated All Glass Distillation Unit, NPL Design, Heater Embedded In Spiral Glass Tube Complete With Heavy Base, Rod, Clamps, Boards Etc.

[Read More](#)

**SKU:**

**Price:** ₹36,000.00

**Stock:** instock

**Categories:** [Pharmacy](#)

### Product Description

Automatic Electrically Heated All Glass Distillation Unit, NPL Design, Heater Embedded In Spiral Glass Tube Complete With Heavy Base, Rod, Clamps, Boards Etc.



## 9"x4"x4" (225x100x100mm)

[Read More](#)



**SKU:**

**Price:** ₹35,000.00

**Stock:** instock

**Categories:** [Biotechnology](#)

## Product Description

### Inner Muffle Size in Inches & mm 14"x7"x5" (350x175x125mm)

Heating elements are made of high temperature kanthal wire. Operated by energy regulator.

[Read More](#)



**SKU:**


**Price:** ₹35,000.00

**Stock:** instock

**Categories:** [Biotechnology](#)



## CAPSULE FILLING MACHINE



(All Contact parts made of SS) A versatile lever operated semi automatic machine for various operations. (I) Plates for putting of capsules. (ii) Removal of caps (iii) Filling of powder by dispensing brush, pressing (iv) Ejection of 100 capsules of 0,00,1, 2, or 3 Any one size on order)

[Read More](#)

**SKU:**

**Price:** ₹35,000.00

**Stock:** instock

**Categories:** [Pharmacy](#)

### Product Description

(All Contact parts made of SS) A versatile lever operated semi automatic machine for various operations. (I) Plates for putting of capsules. (ii) Removal of caps (iii) Filling of powder by dispensing brush, pressing (iv) Ejection of 100 capsules of 0,00,1, 2, or 3 Any one size on order)

[Read More](#)

**SKU:**

**Price:** ₹35,000.00

**Stock:** instock

**Categories:** [Electronics](#)



## Product Description

### Research Model Half Shade, 200mm tube

[Read More](#)

**SKU:**

**Price:** ₹35,000.00

**Stock:** instock

**Categories:** [Physics](#)



## Product Description



# AGN ENTERPRISES

MANUFACTURER & SUPPLIER  
ALL KINDS OF LABORATORY EQUIPMENTS



**Price:** ₹34,800.00

**Stock:** instock

**Categories:** [Biology](#)



## Product Description

---